


Bräcker



RAPID

Traveller inserting tool

RAPID inserting tool Allow for efficient and time-saving insertion of travellers

Bräcker RAPID - the fastest way to insert travellers

Characteristics:

- Slender and easy to use tool, specially suited to small gauges or when ring data is installed
- Possible threading the yarn in the traveller when inserting
- Simple setting with traveller as a gauge
- Ergonomical of travellers simple, untiring inserting

Advantages:


- Fast and easy inserting
- Reduced labor costs
- No traveller losses
- Minimal traveller deformation
- Combined inserting and threading
- Higher productivity
- Easy tool adjustment
- Also suitable for smallest ring diameters and reduced spindle gauges



Bräcker AP system

Magazing system for C-shaped travellers. RAPID offers a capacity of 4 rods (130 to 400 travellers according to size). All rods are identified with traveller type and number

Increase of production / year by using the RAPID



Data

Ne 30, 20.5 TPI, 17'000 RPM

Spinning frames with 1'080 spindles, 25 traveller changes/year

Time to insert traveller: with RAPID 1sec.; by hand 3sec.



Bräcker STRAP system

The traveller is taken up on profile STRAP, up to 10'000 travellers per spool. STRAP system for: ORBIT and SU travellers; C-shaped travellers with fr-Profile